



HID-CertaVision for CDM

HID-CV 35 /S CDM 220-240V

HID-CertaVision electronic ballast for use with ceramic metal-halide (CDM) lamps


Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Inrush Current Width	0.28 ms
Inrush Current Peak (Nom)	22.4 A
Number of Products on MCB (16A Type B) (Nom)	24
Wiring	
Cable Length From Device to Lamp	2 m
Connector Type	Push
Temperature	
Ambient temperature range	-20 °C to 55 °C
T-Case Lifetime (Nom)	80 °C
T-Case Maximum (Max)	80 °C
Mechanical and Housing	
Housing	/S

Approval and Application	
Approval Marks	CE marking
Product Data	
Order product name	HID-CV 35 /S CDM 220-240V
Full product name	HID-CV 35 /S CDM 220-240V
Full product code	694793917416400
Order code	913712006580
Material Nr. (12NC)	913712006580
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6947939174164
Numerator - Packs per outer box	12
EAN/UPC - Case	6947939174171

HID-CertaVision for CDM

Dimensional drawing



Product	C1	A1	A2	B1	B2	B3
HID-CV 35 /S CDM 220-240V	32.1 mm	110.0 mm	98.5 mm	75.0 mm	63.7 mm	4.5 mm

