



HID-PV/DV economy for CPO-CDM

HID-CV 210 /S CPO - CDM 220-240V 50/60HZ

Certavision driver is an electronic driver for CPO or CDM Elite MW lamps – helps create an efficient white-light system.


Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Factor 50% Load (Min)	0.95
Earth Leakage Current (Max)	0.7 mA
Inrush Current Width	700 ms
Inrush Current Peak (Max)	65 A
Wiring	
Cable Length From Device to Lamp	1.5 m
Connector Type	WAGO series 804
Temperature	
Ambient temperature range	-20 °C to 50 °C
T-Case Lifetime (Nom)	80 °C
Mechanical and Housing	
Housing	C2

Approval and Application	
Surge Protection (Common/Differential)	EN61547 kV
Safety Standard	IEC 61347-2-11
Environmental Standard	ISO 14001
Approval Marks	CE marking China Quality Certificate KEUR
Product Data	
Order product name	HID-CV 210 /S CPO - CDM 220-240V 50/60HZ
Full product name	HID-CV 210 /S CPO - CDM 220-240V 50/60HZ
Full product code	694793917426300
Order code	913712008070
Material Nr. (12NC)	913712008070
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6947939174263
Numerator - Packs per outer box	6
EAN/UPC - Case	6947939174270

HID-PV/DV economy for CPO-CDM

Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
HID-CV 210 /S CPO - CDM 220-240V 50/60HZ	4.8 mm	58.0 mm	168.1 mm	156.4 mm	100.0 mm	81.5 mm

