



HID-GreenVision GP-SON

HID-GVIII 750W/P GP-SON 400V NA

Full electronic driver for GP-SON 600/1000W lamps


Product data

Operating and Electrical	
Input Voltage	400 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Inrush Current Width	1.6 ms
Inrush Current Peak (Max)	30 A
Wiring	
Connector Type	JST VH-B Connector
Temperature	
Ambient temperature range	0 °C to 35 °C
T-Case Lifetime (Nom)	70 °C
Controls and Dimming	
Control Interface	None
Mechanical and Housing	
Housing	L 181x151x58

Approval and Application	
Energy Efficiency Index	A2
Surge Protection (Common/Differential)	EN61547 5.7 kV
Safety Standard	EN60928, 60926
Environmental Standard	ISO 14001
Approval Marks	CSA certificate UL certificate
Product Data	
Order product name	HID-GVIII 750W/P GP-SON 400V NA
Full product name	HID-GVIII 750W/P GP-SON 400V NA
Full product code	871869664627400
Order code	913712009361
Material Nr. (12NC)	913712009361
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696646274
Numerator - Packs per outer box	144
EAN/UPC - Case	8718696646281

HID-GreenVision GP-SON

Dimensional drawing



Product	A1	B1	C1
HID-GVIII 750W/P GP-SON 400V NA	181 mm	151 mm	58 mm

