



HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSNE 150L 300I TS

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.


Product data

Operating and Electrical			
Input Voltage	220 V		
Line Frequency	50 Hz		
Input Frequency	50 Hz		
Wiring			
Connector Type	Screw		
Approval and Application			
Approval Marks	CE marking CCC certificate		
Product Data			
Order product name	BSNE 150L 300I TS		

Full product name	BSNE 150L 300I TS	
Full product code	697480505033800	
Order code	913713019359	
Material Nr. (12NC)	913713019359	
Numerator - Quantity Per Pack	1	
EAN/UPC - Product/Case	6974805050338	
Numerator - Packs per outer box	6	
EAN/UPC - Case	6974805050345	

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSNE 150L 300I TS	6.3 mm	64.5 mm	120.0 mm	99.0 mm	75.0 mm



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com 2023, December 29 - data subject to change