



HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSNE 250L 300I TS


The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

General Information		Temperature	
Application Code	L300 ITS	T-Winding (Max)	130 °C
		Delta-T Normal Conditions	70 °C
Operating and Electrical		Approval and Application	
Input Voltage	220 V	Approval Marks	CE marking CCC certificate
Input Frequency	50 Hz		
Power Factor 100% Load (Min)	0.45	Product Data	
Mains Voltage Performance (AC)	-8%~+6%	Full product code	694818229507100
Mains Voltage Safety (AC)	-10%~+10%	Order product name	BSNE 250L 300I TS
Input Current with PF Correction	1.4 A	EAN/UPC - Product	6948182295071
Input Current without PF Correction	3.0 A	Order code	913713019459
Power Factor without PF Compensation (Nom)	0.85	Numerator - Quantity Per Pack	1
Power Losses (Nom)	26.2 W	Numerator - Packs per outer box	6
Wiring		Material Nr. (12NC)	913713019459
Connector Type	Screw	Net Weight (Piece)	2.900 kg
System characteristics			
Rated Ballast-Lamp Power	250 W		

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSNE 250L 300I TS	6.3 mm	64.5 mm	165.0 mm	144 mm	75.0 mm

BSNE 250 L300 ITS

