



HF-Performer III for TL5 lamps

HF-P 154/155 TL5 HO/PL-L III IDC

HF-Performer III TL5 is a sustainable, slim and high-frequency electronic ballast for TL5 and TL5 Eco fluorescent lamps. It is ideal for applications where high energy efficiency is required. The HF-Performer III range has a robust design, meets all relevant international safety and performance standards and is energy-efficient (CELMA EEI A2 BAT).

Product data

General information			
Remarks	UK importer address: Signify Commercial UK Limited, 3, Guildford Business Park, GU2 8XG	Mains voltage performance (AC)	-8% - +6%
Application code	III	Mains voltage safety (AC)	-10% - +10%
Type version	IDC	Earth leakage current (nom.)	0.5 mA
Lamp type	TL5/PL-L	Inrush current width	0.25 ms
Number of lamps	1 piece/unit	Constant wattage deviation	-2% / +2%
Number of products on MCB (16 A type B) (nom.)	28	Ballast factor (nom.)	1
Automatic restart	Yes	Power losses (nom.)	4.5 W
Operating and electrical		Inrush current peak (max.)	24 A
Input Voltage	220 to 240 V	Efficiency at full load [%]	91.86 %
Input frequency	50 to 60 Hz	Wiring	
Operating frequency (nom.)	45 kHz	Connector type input terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]
Ignition method	Programmed Start	Cable capacity output wires mutual (nom.)	200 pF
Crest factor (max.)	1.7	Connector type output terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]
Power factor 100% load (nom.)	0.99	Cable length hot-wiring	0.75 m
Ignition time (max.)	0.9 s	Wire strip length	8.0-9.0 mm

HF-Performer III for TL5 lamps

Dual fixture master/slave	Not applicable [Master/Slave oper. not applicable]
Input terminal cross section	0.50-1.00 mm ²
Output terminal cross section	0.50-1.00 mm ²
Cable capacity output wires to earth (nom.)	200 pF

System characteristics

Rated ballast-lamp power	54/55 W
Rated lamp power on PL-L	54/55 W
System power on PL-L	56W@55 W
Lamp power on PL-L	51.5W@55 W
Power loss on PL-L	4.5W@55 W
Rated lamp power on TL5	54/55 W
System power on TL5	57.5 W@54W; 55.5W@50 W; W
Lamp power on TL5	53 W@54 W
Power loss on TL5	4.5 W@54 W
Rated lamp power on TL5 ECO	50 W
System power on TL5 ECO	54.5 W
Lamp Power on TL5 ECO	51W@50 W
Power loss on TL5 ECO	4.5 W@50 W

Temperature

T-ambient (max.)	60 °C
T-ambient (min.)	-25 °C
T-ambient (min.)	-25 °C
T storage (max.)	80 °C
T storage (min.)	-40 °C
T-case lifetime (nom.)	80 °C
T-case lifetime (nom.)	80 °C
T-Case maximum (max.)	80 °C
T-Ignition (max.)	60 °C
T-Ignition (min.)	-25 °C

Mechanical and housing

Housing	L360x30x22
---------	------------

Emergency operation

Nominal light output after 60 seconds	100% of EBLF
Battery voltage lamp ignition	198-254 V
Normal operating voltage (DC)	220-240 V

Battery voltage lamp operation	176-254
Battery voltage guaranteed operation	176-275 V
Battery voltage guaranteed ignition	186-275 V
Emergency ballast lumen factor (EBLF) (nom.)	100 %
Nominal light output after 5 seconds	50% of EBLF

Approval and application

Energy efficiency index	A2 BAT
IP classification	IP 20 [Ingress Protection 20]
EMI 9 kHz ... 30 MHz	EN 55015 edition 7.1
EMI 30 MHz ... 1,000 MHz	-
Safety standard	IEC 61347-2-3
Performance standard	IEC 60929
Quality standard	ISO 9000:2000
Environmental standard	ISO 14001
Harmonic current emission standard	IEC 61000-3-2
EMC immunity standard	IEC 61547
Vibration standard	IEC68-2-6 F c
Bumps standard	IEC 68-2-29 Eb
Humidity standard	EN 61347-2-3 clause 11
Approval marks	CE marking ENEC certificate VDE-EMV certificate
Temperature marking	Yes
Emergency standard	IEC 60598-2-22
Humming and noise level	< 30 dB(A)

Product data

Full product code	872790086348200
Order product name	HF - P 154/155 TL5 HO/PLL III 220-240V IDC
EAN/UPC – product	8711500998217
Order code	86348200
Local order code	HFP154TL5HOIII
SAP numerator – quantity per pack	1
Numerator – packs per outer box	12
SAP material	913713028266
Net Weight (Piece)	0.252 kg

HF-Performer III for TL5 lamps

Dimensional drawing

A2

Product	D1	C1	A1	A2	B1
HF-P 154/155 TL5 HO/PLL III 220-240V IDC	4.2 mm	22.0 mm	360.0 mm	350.0 mm	30.0 mm

HF-P 154/155 TL5 HO/PLL III 220-240V IDC

