



# **HF-Performer III for TL5 lamps**

### HF-P 254/255 TL5 HO/PLL III 220-240V IDC

HF-Performer III TL5 is a sustainable, slim and high-frequency electronic ballast for TL5 and TL5 Eco fluorescent lamps. It is ideal for applications where high energy efficiency is required. The HF-Performer III range has a robust design, meets all relevant international safety and performance standards and is energy-efficient (CELMA EEI A2 BAT).

#### **Product data**

| General information                     |                  |  |  |
|---|------------------|--|--|
| Application code                        | III              |  |  |
| Type version                            | IDC              |  |  |
| Lamp type                               | TL5/PL-L         |  |  |
| Number of lamps                         | 2 piece/unit     |  |  |
| Number of products on MCB (16 A type B) | 12               |  |  |
| (nom.)                                  |                  |  |  |
| Automatic restart                       | Yes              |  |  |
|   |                  |  |  |
| Operating and electrical                |                  |  |  |
| Input Voltage                           | 220 to 240 V     |  |  |
| Input frequency                         | 50 to 60 Hz      |  |  |
| Operating frequency (nom.)              | 47.5 kHz         |  |  |
| Ignition method                         | Programmed Start |  |  |
| Crest factor (max.)                     | 1.7              |  |  |
| Power factor 100% load (nom.)           | 0.99             |  |  |
| Ignition time (max.)                    | 0.9 s            |  |  |
| Mains voltage performance (AC)          | -8%-+6%          |  |  |
| Mains voltage safety (AC)               | -10%-+10%        |  |  |
| Earth leakage current (nom.)            | 0.5 mA           |  |  |

| Inrush current width                      | 0.35 ms                                 |  |  |  |
|---|---|--|--|--|
| Constant wattage deviation                | -2%/+2%                                 |  |  |  |
| Ballast factor (nom.)                     | 1                                       |  |  |  |
| Power losses (nom.)                       | 5-7 W                                   |  |  |  |
| Inrush current peak (max.)                | 31 A                                    |  |  |  |
| Efficiency at full load [%]               | 92.78 %                                 |  |  |  |
|   |   |  |  |  |
| Wiring                                    |   |  |  |  |
| Connector type input terminals            | WAGO 251 universal connector [ Suitable |  |  |  |
|   | for both automatic wiring (ALF and ADS) |  |  |  |
|   | and manual wiring]                      |  |  |  |
| Cable capacity output wires mutual (nom.) | 200 pF                                  |  |  |  |
| Connector type output terminals           | WAGO 251 universal connector [ Suitable |  |  |  |
|   | for both automatic wiring (ALF and ADS) |  |  |  |
|   | and manual wiring]                      |  |  |  |
| Cable length hot-wiring                   | 0.75 m                                  |  |  |  |
| Wire strip length                         | 8.0-9.0 mm                              |  |  |  |
| Dual fixture master/slave                 | Not applicable [ Master/Slave oper. not |  |  |  |
|   | applicable]                             |  |  |  |
| Input terminal cross section              | 0.50-1.00 mm²                           |  |  |  |

Datasheet, 2022, September 12 data subject to change

## **HF-Performer III for TL5 lamps**

| Output terminal cross section               | 0.50-1.00 mm² |
|---|---------------|
| Cable capacity output wires to earth (nom.) | 200 pF        |
|   | <u>`</u>      |
| System characteristics                      |               |
| Rated ballast-lamp power                    | 54/55 W       |
| Rated lamp power on PL-L                    | 54-55 W       |
| System power on PL-L                        | 107W@55 W     |
| Lamp power on PL-L                          | 102W@55 W     |
| Power loss on PL-L                          | 5W@55 W       |
| Rated lamp power on TL5                     | 54-55 W       |
| System power on TL5                         | 117W@54 W     |
| Lamp power on TL5                           | 111W@54 W     |
| Power loss on TL5                           | 6W@54 W       |
| Rated lamp power on TL5 ECO                 | 50 W          |
| System power on TL5 ECO                     | 102W@50 W     |
| Lamp Power on TL5 ECO                       | 96W@50 W      |
| Power loss on TL5 ECO                       | 6W@50 W       |
|   |               |
| Temperature                                 |               |
| T-ambient (max.)                            | 60 °C         |
| T-ambient (min.)                            | -25 °C        |
| T-ambient (min.)                            | -25 °C        |
| T storage (max.)                            | 80 °C         |
| T storage (min.)                            | -40 °C        |
| T-case lifetime (nom.)                      | 80 ℃          |
| T-case lifetime (nom.)                      | 80 ℃          |
| T-Case maximum (max.)                       | 80 ℃          |
| T-Ignition (max.)                           | 60 ℃          |
| T-Ignition (min.)                           | -25 °C        |
|   |               |
| Mechanical and housing                      |               |
| Housing                                     | L360x30x22    |
|   |               |
| Emergency operation                         |               |
| Nominal light output after 60 seconds       | 100% of EBLF  |
| Battery voltage lamp ignition               | 198-254 V     |
| Normal operating voltage (DC)               | 220-240 V     |
| Battery voltage lamp operation              | 176-254       |

| Battery voltage guaranteed operation  | 176-275 V                            |  |  |
|---------------------------------------|--------------------------------------|--|--|
| Battery voltage guaranteed ignition   | 186-275 V                            |  |  |
| Emergency ballast lumen factor (EBLF) | 100 %                                |  |  |
| (nom.)                                |                                      |  |  |
| Nominal light output after 5 seconds  | 50% of EBLF                          |  |  |
|                                       |                                      |  |  |
| Approval and application              |                                      |  |  |
| Energy efficiency index               | A2 BAT                               |  |  |
| IP classification                     | IP 20 [ Ingress Protection 20]       |  |  |
| EMI 9 kHz 30 MHz                      | EN55015                              |  |  |
| EMI 30 MHz 1,000 MHz                  |                                      |  |  |
| Safety standard                       | IEC 61347-2-3                        |  |  |
| Performance standard                  | IEC 60929                            |  |  |
| Quality standard                      | ISO 9000:2000                        |  |  |
| Environmental standard                | ISO 14001                            |  |  |
| Harmonic current emission standard    | IEC 61000-3-2                        |  |  |
| EMC immunity standard                 | IEC 61547                            |  |  |
| Vibration standard                    | IEC68-2-6 F c                        |  |  |
| Bumps standard                        | IEC 68-2-29 Eb                       |  |  |
| Humidity standard                     | EN 61347-2-3 clause 11               |  |  |
| Approval marks                        | CE marking ENEC certificate VDE-EMV  |  |  |
|                                       | certificate                          |  |  |
| Temperature marking                   | Yes                                  |  |  |
| Emergency standard                    | IEC 60598-2-22                       |  |  |
| Humming and noise level               | < 30 dB(A)                           |  |  |
|                                       |                                      |  |  |
| Product data                          |                                      |  |  |
| Full product code                     | 872790086351200                      |  |  |
| Order product name                    | HF-P 254/255 TL5 HO/PLL III 220-240V |  |  |
|                                       | IDC                                  |  |  |
| EAN/UPC - product                     | 8711500998224                        |  |  |
| Order code                            | 913713028366                         |  |  |
| SAP numerator – quantity per pack     | 1                                    |  |  |
| Numerator – packs per outer box       | 12                                   |  |  |
| SAP material                          | 913713028366                         |  |  |
| Net Weight (Piece)                    | 0.280 kg                             |  |  |
|                                       |                                      |  |  |

### **HF-Performer III for TL5 lamps**

#### Dimensional drawing

A2

| Product                 | D1     | C1      | A1       | A2       | B1      |
|-------------------------|--------|---------|----------|----------|---------|
| HF-P 254/255 TL5 HO/PLL | 4.2 mm | 22.0 mm | 360.0 mm | 350.0 mm | 30.0 mm |
| III 220-240V IDC        |        |         |          |          |         |

HF-P 254/255 TL5 HO/PLL III 220-240V IDC

