



HF-Performer III for TL5 lamps

HF-P 254/255 TL5 HO/PLL III 220-240V IDC

HF-Performer III TL5 is a sustainable, slim and high-frequency electronic ballast for TL5 and TL5 Eco fluorescent lamps. It is ideal for applications where high energy efficiency is required. The HF-Performer III range has a robust design, meets all relevant international safety and performance standards and is energy-efficient (CELMA EEI A2 BAT).

Product data

General information			
Application code	III	Inrush current width	0.35 ms
Type version	IDC	Constant wattage deviation	-2%/+2%
Lamp type	TL5/PL-L	Ballast factor (nom.)	1
Number of lamps	2 piece/unit	Power losses (nom.)	5-7 W
Number of products on MCB (16 A type B) (nom.)	12	Inrush current peak (max.)	31 A
Automatic restart	Yes	Efficiency at full load [%]	92.78 %
Operating and electrical		Wiring	
Input Voltage	220 to 240 V	Connector type input terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]
Input frequency	50 to 60 Hz	Cable capacity output wires mutual (nom.)	200 pF
Operating frequency (nom.)	47.5 kHz	Connector type output terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]
Ignition method	Programmed Start	Cable length hot-wiring	0.75 m
Crest factor (max.)	1.7	Wire strip length	8.0-9.0 mm
Power factor 100% load (nom.)	0.99	Dual fixture master/slave	Not applicable [Master/Slave oper. not applicable]
Ignition time (max.)	0.9 s	Input terminal cross section	0.50-1.00 mm ²
Mains voltage performance (AC)	-8%-+6%		
Mains voltage safety (AC)	-10%-+10%		
Earth leakage current (nom.)	0.5 mA		

HF-Performer III for TL5 lamps

Output terminal cross section	0.50-1.00 mm ²
Cable capacity output wires to earth (nom.)	200 pF

System characteristics

Rated ballast-lamp power	54/55 W
Rated lamp power on PL-L	54-55 W
System power on PL-L	107W@55 W
Lamp power on PL-L	102W@55 W
Power loss on PL-L	5W@55 W
Rated lamp power on TL5	54-55 W
System power on TL5	117W@54 W
Lamp power on TL5	111W@54 W
Power loss on TL5	6W@54 W
Rated lamp power on TL5 ECO	50 W
System power on TL5 ECO	102W@50 W
Lamp Power on TL5 ECO	96W@50 W
Power loss on TL5 ECO	6W@50 W

Temperature

T-ambient (max.)	60 °C
T-ambient (min.)	-25 °C
T-ambient (min.)	-25 °C
T storage (max.)	80 °C
T storage (min.)	-40 °C
T-case lifetime (nom.)	80 °C
T-case lifetime (nom.)	80 °C
T-Case maximum (max.)	80 °C
T-Ignition (max.)	60 °C
T-Ignition (min.)	-25 °C

Mechanical and housing

Housing	L360x30x22
---------	------------

Emergency operation

Nominal light output after 60 seconds	100% of EBLF
Battery voltage lamp ignition	198-254 V
Normal operating voltage (DC)	220-240 V
Battery voltage lamp operation	176-254

Battery voltage guaranteed operation	176-275 V
Battery voltage guaranteed ignition	186-275 V
Emergency ballast lumen factor (EBLF) (nom.)	100 %
Nominal light output after 5 seconds	50% of EBLF

Approval and application

Energy efficiency index	A2 BAT
IP classification	IP 20 [Ingress Protection 20]
EMI 9 kHz ... 30 MHz	EN55015
EMI 30 MHz ... 1,000 MHz	-
Safety standard	IEC 61347-2-3
Performance standard	IEC 60929
Quality standard	ISO 9000:2000
Environmental standard	ISO 14001
Harmonic current emission standard	IEC 61000-3-2
EMC immunity standard	IEC 61547
Vibration standard	IEC68-2-6 F c
Bumps standard	IEC 68-2-29 Eb
Humidity standard	EN 61347-2-3 clause 11
Approval marks	CE marking ENEC certificate VDE-EMV certificate
Temperature marking	Yes
Emergency standard	IEC 60598-2-22
Humming and noise level	< 30 dB(A)

Product data

Full product code	872790086351200
Order product name	HF-P 254/255 TL5 HO/PLL III 220-240V IDC
EAN/UPC – product	8711500998224
Order code	913713028366
SAP numerator – quantity per pack	1
Numerator – packs per outer box	12
SAP material	913713028366
Net Weight (Piece)	0.280 kg

HF-Performer III for TL5 lamps

Dimensional drawing

A2

Product	D1	C1	A1	A2	B1
HF-P 254/255 TL5 HO/PLL III 220-240V IDC	4.2 mm	22.0 mm	360.0 mm	350.0 mm	30.0 mm

HF-P 254/255 TL5 HO/PLL III 220-240V IDC

