PHILIPS Lighting



EB-Certalume for TL-D lamps

EB-Ci 1-2 36W / 1-4 18W 220-240v 50/60Hz

EB-Certalume is the most cost-effective, slim and affordable ballast for reliable operation of a fluorescent lamp. It is also the ideal entry-level product for electromagnetic system users who want to enjoy the benefits offered by electronic ballasts. The cost-saving and reliable EB-Certalume has energy efficiency class A2, and its robust design meets all relevant international safety and performance standards. EB-Certalume is intended for use with indoor lighting fixtures such as recessed luminaires, which are widely used in office, industrial, hotel, restaurant and other applications.

Product data

General Information			
Lamp type	TL-D		
Number of lamps	1-4 piece/unit		
Suitable for outdoor use	No		
Number of products on MCB (16 A type B)	28		
(max.)			
Automatic restart	Yes		
Operating and Electrical			
Input voltage	220-240 V		
Input frequency	50 or 60 Hz		
Operating frequency (nom.)	42-60 kHz		
Ignition method	Warm Start		
Crest factor (max.)	1.7		
Ignition time (nom.)	2.0 s		
Mains voltage performance (AC)	-10%-+10%		
Mains voltage safety (AC)	198264V		


Earth leakage current (max.)	0.5 mA	
Inrush current width	0.35 ms	
Ballast factor (nom.)	1	
Power factor (max.)	0.98	
Power factor (min.)	0.90	
Input power (max.)	70.2 W	
Input power (min.)	21.3 W	
Power losses (max.)	6.2 W	
Power losses (nom.)	3.3 W	
Inrush current peak (max.)	19 A	
Rated lamp power	18-36 W	
Wiring		
Connector type input terminals	Insert	
Cable capacity output wires mutual (max.)	150 pF	
Connector type output terminals	Insert	
Cable length hot-wiring	0.75 m	

EB-Certalume for TL-D lamps

Wire strip length	7.5-8.5 mm			
Input terminal cross section	0.50-1.50 mm²			
Output terminal cross section	0.50-1.50 mm²			
Cable capacity output wires to earth (max.)	150 pF			
Connector type	Insert			
System characteristics				
Rated lamp power on TL-D	18-36 W			
System power on TL-D	21.3-68.2 W			
Lamp power on TL-D	18.0-31.0 W			
Power loss on TL-D	3.3-6.2 W			
Temperature				
T ambient (max.)	50 °C			
T case lifetime (max.)	75 ℃			
T-Case maximum (max.)	75 ℃			
T-Ignition (max.)	50 °C			
T-Ignition (min.)	-10 °C			
Mechanical and Housing				
Housing material	Plastic			
Housing	L210x30x26mm			
Emergency Operation				
Battery voltage lamp ignition	165-253 V			

Approval and Application			
Energy efficiency index	A2		
IP classification	IP 20 [Ingress Protection 20]		
EMI 9 kHz 30 MHz	EN55015		
EMI 30 MHz 1,000 MHz	EN 55015		
Environmental standard	ISO 14001		
Vibration standard	IEC60068-2-6 F c		
Bumps standard	Not specified		
Approval marks	CB Certificate CCC certificate TISI		
	marking PSB certification RCM		
	compliance		
Temperature marking	Yes		
Humming and noise level	< 30 dB(A)		
Product Data			
Full product code	694793913353600		
Order product name	EB-Ci 1-2 36W / 1-4 18W 220-240V		
	50/60Hz		
EAN/UPC – product	6947939133536		
Order code	13353600		
Numerator – quantity per pack	1		
Numerator – packs per outer box	30		
Material no. (12NC)	913713043180		
Net weight (piece)	0.080 kg		

Dimensional drawing



Product	A1	A2	B1	C1	D1
EB-Ci 1-2 36W / 1-4 18W 220-240V	210 mm	200 mm	30 mm	26 mm	4.3 mm
50/60Hz					

EB-Certalume for TL-D lamps



© 2019 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2019, July 9 - data subject to change