

EB-Certalume for TL5 lamps

EB-C 128 TL5 220-240V 50/60Hz

Affordable, reliable, high frequency electronic ballast for TL5 fluorescent lamps, ideal alternative for electromagnetic (EM) ballasts

Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Earth Leakage Current (Max)	0.7 mA

Wiring	
Connector Type Input Terminals	250 manual connector [Suitable for manual wiring and easy release button]
Color Input Terminals	Orange
Color Output Terminals	Grey
Connector Type Output Terminals	250 manual connector [Suitable for manual wiring and easy release button]

Temperature	
T-Case Lifetime (Nom)	75 °C


Mechanical and Housing	
Housing	L 275x20x21

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Energy Efficiency Index	A2
Approval Marks	CCC certificate CB Certificate

Product Data	
Order product name	EB-C 128 TL5 220-240V 50/60Hz
Full product name	EB-C 128 TL5 220-240V 50/60Hz
Full product code	872790088656600
Order code	913713196414
Material Nr. (12NC)	913713196414
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500998927
Numerator - Packs per outer box	50
EAN/UPC - Case	8727900886566

EB-Certalume for TL5 lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
EB-C 128 TL5 220-240V 50/60Hz	4.2 mm	21.0 mm	275.0 mm	265.0 mm	19.8 mm

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.