



EB-Certalume for PLT/C lamps

EB-C 113 PL-T/C 220-240V 50/60Hz

Affordable, reliable, high frequency electronic ballast for 4-pin PL-T and PL-C fluorescent lamps, ideal alternative for electromagnetic (EM) ballasts. The ballast is primarily designed for Indoor application. For outdoor application, the luminaire should be minimum Classland need to be sufficiently protected against water & dust. The installation should also be guard against any lightening surge or any other necessary electrical protection as deemed in such typical installation & application.


Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Number of Products on MCB (16A Type B) (Nom)	
20	
Wiring	
Connector Type Input Terminals	250 manual connector [Suitable for manual wiring and easy release button]
Color Input Terminals	Orange
Color Output Terminals	Grey
Connector Type Output Terminals	250 manual connector [Suitable for manual wiring and easy release button]
Temperature	
T-Case Lifetime (Nom)	65 °C
T-Case Maximum (Max)	65 °C

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Energy Efficiency Index	A2
Approval Marks	CCC certificate CB Certificate
Product Data	
Order product name	EB-C 113 PL-T/C 220-240V 50/60Hz
Full product name	EB-C 113 PL-T/C 220-240V 50/60Hz
Full product code	872790083286000
Order code	913713198414
Material Nr. (12NC)	913713198414
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500997722
Numerator - Packs per outer box	24
EAN/UPC - Case	8727900832860

EB-Certalume for PLT/C lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
EB-C 113 PL-T/C 220-240V 50/60Hz	4.2 mm	31.0 mm	94.0 mm	86.0 mm	72.0 mm

