



# EB-Certalume for PLT/C lamps

## EB-C 226 PL-T/C 220-240V 50/60Hz

Affordable, reliable, high frequency electronic ballast for 4-pin PL-T and PL-C fluorescent lamps, ideal alternative for electromagnetic (EM) ballasts. The ballast is primarily designed for Indoor application. For outdoor application, the luminaire should be minimum Classland need to be sufficiently protected against water & dust. The installation should also be guard against any lightening surge or any other necessary electrical protection as deemed in such typical installation & application.


### Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Number of Products on MCB (16A Type B) (Nom)	
20	
Wiring	
Connector Type Input Terminals	250 manual connector [Suitable for manual wiring and easy release button]
Color Input Terminals	Orange
Color Output Terminals	Grey
Connector Type Output Terminals	250 manual connector [Suitable for manual wiring and easy release button]
Temperature	
T-Case Lifetime (Nom)	65 °C
T-Case Maximum (Max)	65 °C

Mechanical and Housing	
Housing	- [Not Specified]
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Energy Efficiency Index	A2
Approval Marks	CCC certificate CB Certificate
Product Data	
Order product name	EB-C 226 PL-T/C 220-240V 50/60Hz
Full product name	EB-C 226 PL-T/C 220-240V 50/60Hz
Full product code	872790088907900
Order code	913713198914
Material Nr. (12NC)	913713198914
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500998941
Numerator - Packs per outer box	24
EAN/UPC - Case	8727900889079

# EB-Certalume for PLT/C lamps

## Dimensional drawing



Product	D1	C1	A1	A2	B1
EB-C 226 PL-T/C 220-240V 50/60Hz	4.2 mm	31.0 mm	94.0 mm	86.0 mm	72.0 mm

