



# EB-Certalume for TL-D lamps

## EB-C 118 TL-D 220-240V 50/60Hz

EB-Certalume is the most cost-effective, slim and affordable ballast for reliable operation of a fluorescent lamp. It is also the ideal entry-level product for electromagnetic system users who want to enjoy the benefits offered by electronic ballasts. The cost-saving and reliable EB-Certalume has energy efficiency class A2, and its robust design meets all relevant international safety and performance standards. EB-Certalume is intended for use with indoor lighting fixtures such as recessed luminaires, which are widely used in office, industrial, hotel, restaurant and other applications.

### Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Number of Products on MCB (16A Type B) (Nom)	25
Wiring	
Connector Type Input Terminals	250 manual connector [Suitable for manual wiring and easy release button]
Color Input Terminals	Orange
Color Output Terminals	Grey
Connector Type Output Terminals	250 manual connector [Suitable for manual wiring and easy release button]


Temperature	
T-Case Lifetime (Nom)	75 °C
Mechanical and Housing	
Housing	L 150x40x28
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Energy Efficiency Index	A2
Approval Marks	CCC certificate CB Certificate
Product Data	
Order product name	EB-C 118 TL-D 220-240V 50/60Hz
Full product name	EB-C 118 TL-D 220-240V 50/60Hz
Full product code	872790085877800
Order code	85877800
Material Nr. (12NC)	913713199015

EB-Certalume for TL-D lamps

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500998132
Numerator - Packs per outer box	20

EAN/UPC - Case	8727900858778
----------------	---------------

Dimensional drawing



Product	D1	C1	A1	A2	B1
EB-C 118 TL-D 220-240V 50/60Hz	4.2 mm	28.0 mm	150.0 mm	140.0 mm	40.0 mm

