



MileWide²

BRP435 LED115-4S/740II SI DM12 D9 48ST25

MileWide 2 - side entry - LED module 11500 lm - 740 neutral white - Safety class II (II) - Distribution medium 12 - Silver - Marine salt protected coating - Cord 0.5 m with cable connector 5-pole - Side-entry for diameter 48 mm

Many municipal authorities are embracing the benefits of contemporary outdoor lighting. These include a more attractive urban environment and increased comfort, safety and security for the public. Not to mention the positive impact on environmental protection and city branding. Together with Holscher Design, Philips has developed MileWide², the successor to the highly popular MileWide family. Featuring a range of dedicated masts and brackets, the pure, clean design of MileWide² integrates perfectly with today's and tomorrow's cityscape. With its high-quality finish and high level of lighting performance, MileWide² is suitable for a wide range of applications, ranging from traffic roads to city centers. Multi-layer optics provide a uniform light distribution and reduced glare, enabling direct replacement of HID solutions without compromising on spacing, mounting height or light quality.

Product data

General Information	
Lamp family code	LED115 [LED module 11500 lm]
Light source color	740 neutral white
Light source replaceable	Yes
Number of gear units	1 unit
Driver/power unit/transformer	PSD [Power supply unit with DALI interface]
Driver included	Yes
Optical cover/lens type	FG [Flat glass]
Luminaire light beam spread	-
Control interface	DALI

Connection	CU5 [Connection unit 5-pole]
Cable	Cord 0.5 m with cable connector 5-pole
Protection class IEC	Safety class II (II)
Coating	Marine salt protected coating
Flammability mark	NO [-]
CE mark	CE mark
ENEC mark	ENEC mark
Warranty period	3 years + 2 years upon registration
Optic type outdoor	Distribution medium 12

Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components
Constant light output	No
Number of products on MCB of 16 A type B	10
EU RoHS compliant	Yes
Light source engine type	LED
Serviceability class	Class A, luminaire is equipped with serviceable parts (when applicable): LED board, driver, control units, surge protection device, optics, front cover and mechanical parts
Product family code	BRP435 [MileWide 2 side entry]

Light Technical

Upward light output ratio	0.03
Standard tilt angle posttop	-
Standard tilt angle side entry	-

Operating and Electrical

Input Voltage	220/240 V
Input Frequency	50 to 60 Hz
Inrush current	45 A
Inrush time	285 ms
Power Factor (Min)	0.98

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover/lens material	Glass
Fixation material	Aluminum
Mounting device	48S [Side-entry for diameter 48 mm]
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall length	610 mm

Overall width	276 mm
Overall height	108 mm
Effective projected area	0.049 m ²
Color	Silver
Dimensions (Height x Width x Depth)	108 x 276 x 610 mm (4.3 x 10.9 x 24 in)

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 6 kV common mode

Initial Performance (IEC Compliant)


Initial luminous flux (system flux)	9660 lm
Luminous flux tolerance	+/-7%
Initial LED luminaire efficacy	137 lm/W
Init. Corr. Color Temperature	4000 K
Init. Color Rendering Index	≥70
Initial chromaticity	(0.380, 0.380) SDCM <5
Initial input power	71 W
Power consumption tolerance	+/-11%

Application Conditions


Ambient temperature range	-40 to +50 °C
Maximum dim level	Programmable

Product Data

Full product code	871869958041400
Order product name	BRP435 LED115-4S/740II SI DM12 D9 48ST25
EAN/UPC - Product	8718699580414
Order code	58041400
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	919008633654
Net Weight (Piece)	5.740 kg



Dimensional drawing



MileWide2 BPP/BRP435

