



ComboCC Gen 4.0

ZJS401 HYC 150W 12V SOLAR

Combo CC Gen 4.0 is most comprehensive range of solar charge controllers suitable for solar lighting in major, intermediate and minor roads in off-grid and hybrid applications. High system efficacy, optimized design and long life ensures lower cost of ownership. Configurable and easy to operate with remote monitoring and control ready.

Combo CC Gen 4.0 is most comprehensive range of solar charge controllers suitable for solar lighting in major, intermediate and minor roads in off-grid and hybrid applications. High system efficacy, optimized design and long life ensures lower cost of ownership. Configurable and easy to operate with remote monitoring and control ready.

Product data

General Information	
Cable	Connectors: battery, charge controller interface, AC Connection Cable
Warranty period	2 years
Operating and Electrical	
Input Voltage	170 to 300 V
Input Frequency	50 Hz
Battery type	Multiple
Charge controller type	MPPT
Charge controller wattage	140 W
Cable connection kit	Excluded

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Overall length	149 mm
Overall width	111 mm
Overall height	57.7 mm
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Surge Protection (Common/Differential)	Surge protection level until 4 kV Differential mode kV

ComboCC Gen 4.0

Initial Performance (IEC Compliant)

Initial LED luminaire efficacy 170 lm/W

Application Conditions

Ambient temperature range -20 to +45 °C

Grid connection type Hybrid

Product Data

Order product name ZJS401 HYC 150W 12V SOLAR

Order code 919415811128

Numerator - Quantity Per Pack 1


Numerator - Packs per outer box 10

Material Nr. (12NC) 919415811128

Net Weight (Piece) 1.600 kg

IP65

Dimensional drawing



Solar Chargers

