



# GreenPerform DN391/392/393/394/ 395 downlight

## DN 392B LED10S-4000 PSU WH

GreenPerform is a high performance Led downlight family suitable for use in a series of Lighting applications in Office, Retail and General Area Lighting. Available in a wide variety of lumen packs, color temp and options of all type of dimming(Phase Cut/Analogue/DALI), GreenPerform becomes the perfect solution for downlight applications for professional users.

### Warnings and Safety

- Meant for use in Indoor environment only

### Product data

General Information		Optical cover type	
Driver included	Yes	Polycarbonate	
Light source engine type	LED	Luminaire light beam spread	
Warranty period	3 years	120°	
Flammability mark	For mounting on normally flammable surfaces		
Light Technical		Operating and Electrical	
Luminous Flux	1,000 lm	Input Voltage	220-240 V
Correlated Color Temperature (Nom)	4000 K	Line Frequency	50 Hz
Luminous Efficacy (rated) (Nom)	100 lm/W	Power Consumption	10.6 W
Color rendering index (CRI)	>80	Power Factor (Fraction)	0.9
Beam angle of light source	120 degree(s)	Temperature	
Light source color	840 neutral white	Ambient temperature range	
Optic type	-	0 to +45 °C	
		Controls and Dimming	
		Dimmable	
		No	

GreenPerform DN391/392/393/394/395 downlight

Control interface	-
Mechanical and Housing	
Housing Material	Aluminum Alloy
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	White
Mounting device	Spring clip for recess mounting
Overall height	70 mm
Overall diameter	150 mm
Material	Aluminum
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Surge Protection (Common/Differential)	2.5 kV
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)	
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Median useful life L70B50	40,000 hour(s)
Product Data	
Order product name	DN 392B LED10S-4000 PSU WH
Full product name	DN 392B LED10S-4000 PSU WH
Order code	919515810484
Material Nr. (12NC)	919515810484
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	8

Dimensional drawing

Product: GNI  
Type: DN391B / DN392B / DN393B / DN394B/ DN395B  
Application: Indoor

