



GreenLine V2 Solar

solarEquip.BRP4092445WMAXCWMRPCS124VPR
OG

Configure lumen pack, change the dimming profile, , monitor health, read analog parameters from ground level using simple easy to use android app.

Product data

| General Information | |
|------------------------------------|--|
| Driver included | Yes |
| Warranty period | 3 years |
| Light Technical | |
| Correlated Color Temperature (Nom) | 5700 K |
| Color rendering index (CRI) | >70 |
| Optical cover type | Polycarbonate |
| Operating and Electrical | |
| Charge controller type | MPPT |
| Charge controller wattage | 45 W |
| Cable connection kit | Included |
| Cable | Cord 0.5 m 4 core for battery and panel, without connectors and additional 1.0 m cable for solar panel included in the box |
| Temperature | |
| Ambient temperature range | 0 to +35 °C |

| Controls and Dimming | |
|---------------------------------------|--|
| Dimmable | Yes |
| Configurability | Configurable |
| Control interface | BLE |
| Mechanical and Housing | |
| Overall length | 416 mm |
| Overall width | 203 mm |
| Overall height | 75 mm |
| Dimensions (Height x Width x Depth) | 75 x 203 x 416 mm |
| Material | Pressure die cast aluminum |
| Approval and Application | |
| Ingress protection code | IP66 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK05 [0.7 J] |
| Over Time Performance (IEC Compliant) | |
| Median useful life | 50,000 hour(s) |
| L70B50 | |
| Application Conditions | |
| Solar dimming profile | Configurable through mobile app |

GreenLine V2 Solar

| | |
|----------------------|--|
| Grid connection type | Hybrid |
| Battery location | Outside Luminaire |
| Product Data | |
| Order product name | solarEquip.BRP4092445WMAXCWMRPCS124VPROG |
| Full product name | solarEquip.BRP4092445WMAXCWMRPCS124VPROG |
| Order code | 919515811045 |

| | |
|-----------------------|--------------|
| Material Nr. (12NC) | 919515811045 |
| Numerator - Quantity | 1 |
| Per Pack | |
| Numerator - Packs per | 1 |
| outer box | |

Dimensional drawing

Dimensions

