



# SunStay

## BRP710 LED20 CW MR S1 12V 35MO FDIM50 So

Integrated solar street light with Lithium Ferro Phosphate battery, solar panel, charger and PIR sensor built into the luminaire. Pressure die cast aluminium for sturdiness and long life. Specially designed pole mounting bracket allows different tilt angles, lateral and pole top mounting.

### Product data

General Information	
Light source color	Cool white
Driver included	Yes
Optical cover/lens type	UV stabilized Polycarbonate cover
Operating and Electrical	
Battery type	Lithium Ferro Phosphate
Battery ampere hour	13.6 Ah
Battery voltage	12.8 V
Battery charging & discharging cycles	2000
Panel type	Mono crystalline
Panel voltage	17 Vmp, 21 Voc V
Panel peak wattage	35 W
Charge controller type	MPPT
Controls and Dimming	
Dimmable	Yes
Configurability	Factory Configurable
Mechanical and Housing	
Housing Material	Aluminium pressure die cast
Overall length	684 mm
Overall width	369 mm

Overall height	156 mm
Color	Gray
Approval and Application	
Ingress protection code	IP65 [ Dust penetration-protected, jet-proof]
Initial Performance (IEC Compliant)	
Initial luminous flux (system flux)	2000 lm
Initial LED luminaire efficacy	175 lm/W
Init. Corr. Color Temperature	5700 K
Init. Color Rendering Index	>70
Initial input power	11.5 W
Application Conditions	
Ambient temperature range	0 to +35 °C
Ambient temperature range for charging	0 to +45 °C
Ambient temperature range for discharging (when light is on)	-20 to +35 °C
Solar dimming profile	5hrs 100% + 7 hrs 50%
Grid connection type	Off grid
Battery location	Inside Luminaire

## Product Data

<b>Order product name</b>	BRP710 LED20 CW MR S1 12V 35MO FDIM50 So
<b>EAN/UPC - Product</b>	8710163354217
<b>Order code</b>	919515812631
<b>Numerator - Quantity Per Pack</b>	1

<b>Numerator - Packs per outer box</b>	1
<b>Material Nr. (12NC)</b>	919515812631
<b>Net Weight (Piece)</b>	10.500 kg

