



# SunStay

## BRP710 LED30 CW MR HY SOLAR IN

Integrated solar street light with Lithium Ferro Phosphate battery, solar panel and charger built into the luminaire. Pressure die cast aluminium for sturdiness and long life. Specially designed pole mounting bracket allows different tilt angles, lateral and pole top mounting.

### Product data

<b>General Information</b>	
Driver included	Yes
CE mark	CE mark
<b>Light Technical</b>	
Luminous Flux	3,000 lm
Correlated Color Temperature (Nom)	5700 K
Luminous Efficacy (rated) (Nom)	175 lm/W
Color rendering index (CRI)	>70
Optical cover type	UV stabilized Polycarbonate cover
<b>Operating and Electrical</b>	
Input Voltage	240 V
Line Frequency	50 Hz
Battery type	Lithium Ferro Phosphate
Battery ampere hour	20 Ah
Battery voltage	12.8 V
Battery charging & discharging cycles	2000
Panel type	Mono crystalline
Panel voltage	17 Vmp, 21 Voc V
Panel peak wattage	35 W
Charge controller type	MPPT
Charge controller wattage	17 W

Cable connection kit	Included
Cable	Cable 0.8m, 2-core, 1.5mm2
<b>Temperature</b>	
Ambient temperature range	0 to +35 °C
<b>Controls and Dimming</b>	
Dimmable	Yes
Configurability	Factory Configurable
<b>Mechanical and Housing</b>	
Housing Color	RAL 7011
Overall length	684 mm
Overall width	369 mm
Overall height	156 mm
Dimensions (Height x Width x Depth)	156 x 369 x 684 mm
Material	Pressure die cast aluminum
<b>Approval and Application</b>	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]

Surge Protection (Common/Differential)	Surge protection level until 4 kV
Over Time Performance (IEC Compliant)	
Median useful life L70B50	50,000 hour(s)
Application Conditions	
Ambient temperature range for charging	0 °C to +45 °C
Ambient temperature range for discharging (when light is on)	-20 °C to +35 °C
Solar dimming profile	100% Dusk to dawn
Grid connection type	Hybrid

Battery location	Integrated
Product Data	
Order product name	BRP710 LED30 CW MR HY SOLAR IN
Full product name	BRP710 LED30 CW MR HY SOLAR IN
Order code	919515813174
Material Nr. (12NC)	919515813174
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

