



# SunStay

## BRP710 LED60 CW MR HY FDIM20 SOLAR

Integrated solar street light with Lithium Ferro Phosphate battery, solar panel and charger built into the luminaire. Pressure die cast aluminium for sturdiness and long life. Specially designed pole mounting bracket allows different tilt angles, lateral and pole top mounting.

### Product data


General Information	
Driver included	Yes
CE mark	CE mark
Warranty period	3 years
EU RoHS compliant	Yes
Light Technical	
Luminous Flux	6,000 lm
Correlated Color Temperature (Nom)	5700 K
Luminous Efficacy (rated) (Nom)	175 lm/W
Color rendering index (CRI)	>70
Optical cover type	UV stabilized Polycarbonate cover
Operating and Electrical	
Input Voltage	240 V
Line Frequency	50 Hz
Battery type	Lithium Ferro Phosphate
Battery ampere hour	30 Ah
Battery voltage	12.8 V
Battery charging & discharging cycles	2000
Panel type	Mono crystalline
Panel voltage	17 Vmp, 21 Voc V
Panel peak wattage	60 W

Charge controller type	MPPT
Charge controller wattage	35 W
Cable connection kit	Included
Cable	Cable 0.8m, 2-core, 1.5mm <sup>2</sup>
Temperature	
Ambient temperature range	0 to +35 °C
Controls and Dimming	
Dimmable	Yes
Configurability	Factory Configurable
Mechanical and Housing	
Housing Color	RAL 7011
Overall length	757 mm
Overall width	511 mm
Overall height	188 mm
Dimensions (Height x Width x Depth)	188 x 511 x 757 mm
Material	Pressure die cast aluminum
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]

Surge Protection (Common/Differential)	Surge protection level until 4 kV
Over Time Performance (IEC Compliant)	
Median useful life L70B50	50,000 hour(s)
Application Conditions	
Ambient temperature range for charging	0 °C to +45 °C
Ambient temperature range for discharging (when light is on)	-20 °C to +35 °C
Solar dimming profile	4hrs 100% + 8 hrs 20%
Grid connection type	Hybrid
Battery location	Inside Luminaire

Product Data	
Order product name	BRP710 LED60 CW MR HY FDM20 SOLAR
Full product name	BRP710 LED60 CW MR HY FDM20 SOLAR
Full product code	871951450185000
Order code	919515813979
Material Nr. (12NC)	919515813979
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514501850
Numerator - Packs per outer box	1
EAN/UPC - Case	8719514501850

## Dimensional drawing



**PHILIPS**

