



# SunStay

## BRP710 LED30 CW Housing KIT Solar

Integrated solar street light with Lithium Ferro Phosphate battery, solar panel, charger and PIR sensor built into the luminaire. Pressure die cast aluminium for sturdiness and long life. Specially designed pole mounting bracket allows different tilt angles, lateral and pole top mounting.

### Product data

General Information	
Light source color	Cool white
Driver included	Yes
Optical cover/lens type	UV stabilized Polycarbonate cover
Operating and Electrical	
Battery type	Lithium Ferro Phosphate
Battery ampere hour	20 Ah
Battery voltage	12.8 V
Battery charging & discharging cycles	2000
Panel type	Mono crystalline
Panel voltage	17 Vmp, 21 Voc V
Panel peak wattage	35 W
Charge controller type	MPPT
Controls and Dimming	
Dimmable	Yes
Configurability	Factory Configurable
Mechanical and Housing	
Housing Material	Aluminium pressure die cast
Overall length	684 mm
Overall width	369 mm

Overall height	156 mm
Color	Gray
Approval and Application	
Ingress protection code	IP65 [ Dust penetration-protected, jet-proof]
Initial Performance (IEC Compliant)	
Initial luminous flux (system flux)	3000 lm
Initial LED luminaire efficacy	175 lm/W
Init. Corr. Color Temperature	5700 K
Init. Color Rendering Index	>70
Initial input power	17 W
Application Conditions	
Ambient temperature range	0 to +35 °C
Ambient temperature range for charging	0 to +45 °C
Ambient temperature range for discharging (when light is on)	-20 to +35 °C
Solar dimming profile	30% Dusk to dawn, 100% on motion. ( Sensor disabled for 5 Hrs, after 5 Hrs)
Grid connection type	Off grid

## SunStay

Battery location	Inside Luminaire
<b>Product Data</b>	
Order product name	BRP710 LED30 CW Housing KIT Solar
EAN/UPC - Product	8710163354354
Order code	919615811179
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	1
Material Nr. (12NC)	919615811179
Net Weight (Piece)	8.000 kg

