



Standard Extra Low Voltage A60

STAN ELV 60W E27/BRC 50V A60 CL 1CT

Clear lamp (A-bulb) for operation on voltages of 12, 24, 42 and 50 V

Product data

General Information	
Cap base	E27 [E27]
Operating position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime (nom.)	1000 h
Switching cycle	4000X

Light Technical	
Luminous flux (nom.)	810 lm
Luminous flux (rated) (nom.)	810 lm
Correlated colour temperature (nom.)	2700 K
Color rendering index (nom.)	100

Operating and Electrical	
Power (Rated) (Nom)	60.0 W
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	instant full light
Voltage (Nom)	50 V

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb finish	Clear
Cap base information	Brass [Brass Cap]

Approval and Application	
Energy efficiency label (EEL)	D
Energy Consumption kWh/1000 h	60 kWh

Product Data	
Full product code	871150010188484
Order product name	Standard ELV 60W E27/BRC 50V A60 CL 1CT
EAN/UPC – product	8711500101884
Order code	10188484
Numerator – quantity per pack	1
Numerator – packs per outer box	120
Material no. (12NC)	920021025303
Net weight (piece)	28.000 g
ILCOS Code	IAA/C-60-50-E27-60

Standard Extra Low Voltage A60

Dimensional drawing



Product	D (max)	C (max)
Standard ELV 60W E27/BRC 50V A60 CL 1CT	60 mm	107.5 mm

ELV 60W E27/BRC 50V A60 CL

