



# InfraRed Industrial Heat Incandescent

## BR125 IR 250W E27 230-250V CL 1CT/10

The Philips infrared incandescent reflector lamps are designed to work in the toughest environment such as farm, bathroom or kitchen and their nearest surrounding. They have a reinforced construction thanks to hard glass use. Their compact form and universal cap base allow them to be used with any suitable equipment. A very good method of generating warmth is by using heat lamps. The Philips infrared lamps provide direct, draught-free warmth to the animals, people, but also food. These benefits have made farmers, consumers and cooks around the world choose Philips infrared lamps, because they are the sturdiest, most efficient lamps available for these applications.


### Product data

General Information		Bulb Material	Hard Glass
Cap-Base	E27	Bulb Shape	BR125
Operating Position	UNIVERSAL [Any or Universal (U)]	<b>Product Data</b>	
Nominal lifetime	5,000 h	Order product name	BR125 IR 250W E27 230-250V CL 1CT/10
Rated Lifetime (Hours)	5,000 h	Full product name	BR125 IR 250W E27 230-250V CL 1CT/10
Lighting Technology	Incandescent	Full product code	871150057523425
<b>Operating and Electrical</b>		Local code description	IR250CH
Power Consumption	250 W	Order code	923212143801
Voltage (Nom)	230-250 V	Material Nr. (12NC)	923212143801
<b>Controls and Dimming</b>		Local order code	IR250CH
Dimmable	Yes	Numerator - Quantity Per Pack	1
<b>Mechanical and Housing</b>		EAN/UPC - Product/Case	8711500575234
Bulb Finish	Clear	Numerator - Packs per outer box	10
		EAN/UPC - Case	8727900209266

# InfraRed Industrial Heat Incandescent

---

## Dimensional drawing



Product	D	C (max)
BR125 IR 250W E27 230-250V CL 1CT/10	125 mm	173 mm

