



# InfraRed Industrial Heat Incandescent

## R125 IR 300W E27 230-250V CL 1CT/10

The Philips infrared incandescent reflector lamps are designed to work in the toughest environment such as farm, bathroom or kitchen and their nearest surrounding. They have a reinforced construction thanks to hard glass use. Their compact form and universal cap base allow them to be used with any suitable equipment. A very good method of generating warmth is by using heat lamps. The Philips infrared lamps provide direct, draught-free warmth to the animals, people, but also food. These benefits have made farmers, consumers and cooks around the world choose Philips infrared lamps, because they are the sturdiest, most efficient lamps available for these applications.


### Product data

General Information	
Cap base	E27 [E27]
Operating position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	5,000 h
Rated Lifetime (Hours)	5,000 h
Lighting Technology	Incandescent
Operating and Electrical	
Power Consumption	300 W
Voltage (nom.)	230-250 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Lamp Finish	Clear

Bulb material	Hard Glass
Bulb shape	R125 [R 125 mm]
Product Data	
Order product name	R125 IR 300W E27 230-250V CL 1CT/10
Full product name	R125 IR 300W E27 230-250V CL 1CT/10
Full EOC	871150012656625
Order code	12656625
Material no. (12 NC)	923223043807
Local order code	IR300CH
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500126566
Numerator – packs per outer box	10
EAN/UPC - Case	8711500141088

# InfraRed Industrial Heat Incandescent

## Dimensional drawing



Product	D	C (max)
R125 IR 300W E27 230-250V CL 1CT/10	125 mm	179 mm

