



InfraRed Industrial Heat Incandescent

R125 IR 375W E27 230-250V CL 1CT/10


The Philips infrared incandescent reflector lamps are designed to work in the toughest environment such as farm, bathroom or kitchen and their nearest surrounding. They have a reinforced construction thanks to hard glass use. Their compact form and universal cap base allow them to be used with any suitable equipment. A very good method of generating warmth is by using heat lamps. The Philips infrared lamps provide direct, draught-free warmth to the animals, people, but also food. These benefits have made farmers, consumers and cooks around the world choose Philips infrared lamps, because they are the sturdiest, most efficient lamps available for these applications.

Product data

| General Information | | Bulb Material | Hard Glass |
|---------------------------------|----------------------------------|---------------------------------|-------------------------------------|
| Cap-Base | E27 [E27] | Bulb Shape | R125 [R 125mm] |
| Operating Position | UNIVERSAL [Any or Universal (U)] | Product Data | |
| Nominal lifetime | 5,000 h | Order product name | R125 IR 375W E27 230-250V CL 1CT/10 |
| Rated Lifetime (Hours) | 5,000 h | Full product name | R125 IR 375W E27 230-250V CL 1CT/10 |
| Lighting Technology | Incandescent | Full product code | 871150012659725 |
| Operating and Electrical | | Local code description | IR375CH |
| Power Consumption | 375 W | Order code | 923223543807 |
| Voltage (Nom) | 230-250 V | Material Nr. (12NC) | 923223543807 |
| Controls and Dimming | | Local order code | IR375CH |
| Dimmable | Yes | Numerator - Quantity Per Pack | 1 |
| Mechanical and Housing | | EAN/UPC - Product/Case | 8711500126597 |
| Bulb Finish | Clear | Numerator - Packs per outer box | 10 |
| | | EAN/UPC - Case | 8711500141118 |

InfraRed Industrial Heat Incandescent

Dimensional drawing



| Product | D | C (max) |
|-------------------------------------|--------|---------|
| R125 IR 375W E27 230-250V CL 1CT/10 | 125 mm | 183 mm |

