



Reflector diam 50 mm

Refl 40W E14 230V NR50 30D 1CT/30

Reflector lamps based on advanced spotlighting technology


Product data

General Information	
Cap-Base	E14 [E14]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Beam Angle (Nom)	30 degree(s)
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	40 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	NR50 [NR 50mm]
Product Data	
Order product name	Refl 40W E14 230V NR50 30D 1CT/30
Full product name	Refl 40W E14 230V NR50 30D 1CT/30
Full product code	871150005415978
Order code	923338544203
Material Nr. (12NC)	923338544203
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500054159
Numerator - Packs per outer box	30
EAN/UPC - Case	8711500343741


Reflector diam 50 mm

Dimensional drawing



Product	D
Refl 40W E14 230V NR50 30D 1CT/30	50 mm

Photometric data



Light Distribution Diagram - Refl 40W E14 230V NR50 30D 1CT/30

