



PAR38

PAR38 80W E27 230V PAR38 Spot 12D 1CT/12

Lampu reflektor kaca pres berdiameter 121 mm dengan intensitas cahaya yang tinggi


Product data

Informasi Umum	
Tutup-Dasar	E27 [E27]
Posisi Pengoperasian	UNIVERSAL [Setiap atau Universal (U)]
Nominal masa pakai	2.000 jam
Siklus Sakelar	8.000
Nilai Masa Pakai (Jam)	2.000 jam
Teknologi Pencahayaan	Incandescent
Teknis Lampu	
Sudut Cahaya (Nom)	12 °
Suhu Warna Terkorelasi (Nom)	2700 K
Indeks renderasi warna (CRI)	100
Fluks Cahaya dalam Kerucut 90° (Terukur)	655 lm
Pengoperasian dan Kelistrikan	
Konsumsi Daya	80,0 W
Waktu Mulai (Nom)	0,0 s
Waktu pemanasan hingga 60% cahaya	cahaya penuh seketika s
Faktor Daya (Fraksi)	1
Tegangan (Nom)	230 V
Tegangan (Nom)	230 V
Kontrol dan Peredupan	
Dapat diredupkan	Ya

Mekanis dan Housing	
Bentuk Bohlam	PAR38 [PAR 4,75 inci/121 mm]
Penyetujuan dan Aplikasi	
Penggunaan Energi kWh/1000 h	80 kWh
Data Produk	
Nama produk pesanan	PAR38 80W E27 230V PAR38 Spot 12D 1CT/12
Nama lengkap produk	PAR38 80W E27 230V PAR38 Spot 12D 1CT/12
Kode produk lengkap	871150060037000
Kode urutan	923810244214
No. Material (12NC)	923810244214
Numerator - Jumlah Per Pak	1
EAN/UPC - Produk/Kantung	8711500600370
Numerator - Pak per kotak bagian luar	12
EAN/UPC - Kantung	8718291115755


PAR38

Dimensional drawing



Product	D (max)	C (max)
PAR38 80W E27 230V PAR38 Spot 12D 1CT/12	123 mm	137 mm

Photometric data



Light Distribution Diagram - PAR38 80W E27 230V PAR38 Spot 12D 1CT/12

