



PAR38

PAR38 120W E27/51 220-240V PAR38 30D 1CT

Pressed-glass 121 mm diameter reflector lamps of high luminous intensity

Product data

| General Information | |
|-----------------------------|----------------------------------|
| Cap-Base | E27/51 [E27/51] |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime | 2,000 hour(s) |
| Rated Lifetime (Hours) | 2,000 hour(s) |
| Lighting Technology | Incandescent |
| Light Technical | |
| Beam Angle (Nom) | 30 degree(s) |
| Luminous Flux | 1,150 lm |
| Color rendering index (CRI) | 100 |
| Operating and Electrical | |
| Power Consumption | 120 W |
| Starting Time (Nom) | 0.0 s |
| Voltage (Nom) | 220-240 V |

| Mechanical and Housing | |
|---------------------------------|--|
| Bulb Shape | PAR38 [PAR 4.75 inch/121mm] |
| Product Data | |
| Order product name | PAR38 120W E27/51 220-240V PAR38 30D 1CT |
| Full product name | PAR38 120W E27/51 220-240V PAR38 30D 1CT |
| Full product code | 871016317087901 |
| Order code | 923815643301 |
| Material Nr. (12NC) | 923815643301 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8710163170879 |
| Numerator - Packs per outer box | 12 |
| EAN/UPC - Case | 8718291115847 |


PAR38

Dimensional drawing



| Product | D | C (max) | C1 |
|--|--------|---------|--------|
| PAR38 120W E27/51 220-240V PAR38 30D 1CT | 121 mm | 137 mm | 123 mm |

Photometric data



Light Distribution Diagram - PAR38 120W E27/51 220-240V PAR38 30D 1CT

