



# Halogen non-reflector

## BRL 7027 50W 12V 100PK

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.

### Product data

General Information	
Base	G6.35 [ G6.35]
Philips Code	7027
ANSI Code	BRL-BCD
LIF Code	A1/220
Operating Position	Base Down +/- 90 D [ Base Down +/- 90 D]
Main Application	Projection
Life to 50% Failures (Nom)	50 h

  

Light Technical	
Luminous Flux (Rated) (Nom)	1600 lm
Color Rendering Index (Nom)	100

  

Operating and Electrical	
Power (Rated) (Nom)	50 W
Voltage (Nom)	12 V

  

Mechanical and Housing	
Bulb Material	Quartz-UV Open

Filament Shape	Flat
Filament Dimensions WxH	3.3x1.6

  

Luminaire Design Requirements	
Bulb Temperature (Max)	900 °C
Pinch Temperature (Max)	400 °C

  

Product Data	
Order product name	7027 50W G6.35 12V 1CT/10X10F
EAN/UPC - Product	8711500409829
Order code	316273
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	100
Material Nr. (12NC)	923870217103
Net Weight (Piece)	0.002 kg

# Halogen non-reflector

## Dimensional drawing



### Product

7027 50W G6.35 12V 1CT/10X10F

7027 50W G6.35 12V

