



Halogen non-reflector

6550 150W G6.35 15V 1CT/10X10F

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.

Product data

General Information	
Cap-Base	G6.35 [G6.35]
Philips Code	6550
ANSI Code	EVB-BRJ
LIF Code	A1/234
Operating Position	S90 [Base Down +/- 90D]
Main Application	Projection
Life to 50% Failures (Nom)	50 h

Light Technical	
Luminous Flux (Rated) (Nom)	5600 lm
Correlated Color Temperature (Nom)	3450 K
Color Rendering Index (Nom)	100

Operating and Electrical	
Power (Rated) (Nom)	150 W
Voltage (Nom)	15 V


Mechanical and Housing	
Bulb Material	Quartz-UV Open
Filament Shape	Flat
Filament Dimensions WxH	4.8x3.0

Luminaire Design Requirements	
Bulb Temperature (Max)	900 °C
Pinch Temperature (Max)	400 °C

Product Data	
Full product code	871150040984350
Order product name	6550 150W G6.35 15V 1CT/10X10F
EAN/UPC - Product	8711500409843
Order code	923870618503
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	100
Material Nr. (12NC)	923870618503
Net Weight (Piece)	0.002 kg

Halogen non-reflector

Dimensional drawing



6550 150W G6.35 15V

Product

6550 150W G6.35 15V 1CT/10X10F

