



# HalogenA IDE

## HALA IDE 500W E40 230V CL 1CT/6

Mains-voltage high-wattage double-envelope giving a white halogen light


### Product data

General Information	
Cap base	E40 [ E40]
Operating position	UNIVERSAL [ Any/Universal]
Nominal lifetime (nom.)	2000 h
Switching cycle	8000X
Light Technical	
Luminous flux (nom.)	10250 lm
Luminous flux (rated) (nom.)	10250 lm
Correlated colour temperature (nom.)	2900 K
Luminous efficacy (rated) (nom.)	20.5 lm/W
Color rendering index (nom.)	100
LLMF at end of nominal lifetime (min.)	80 %
Operating and Electrical	
Power (Rated) (Nom)	500.0 W
Lamp current (nom.)	2.17 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	instant full light
Power factor (nom.)	1
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	yes
Mechanical and Housing	
Bulb finish	Clear
Approval and Application	
Energy efficiency label (EEL)	D
Energy Consumption kWh/1000 h	500 kWh
Product Data	
Full product code	871150049126810
Order product name	HalogenA IDE 500W E40 230V CL 1CT/6
EAN/UPC – product	8711500491268
Order code	49126810
Numerator – quantity per pack	1
Numerator – packs per outer box	6
Material no. (12NC)	923900144240
Net weight (piece)	141.000 g
ILCOS Code	HEGT-500-230-e40

# HalogenA IDE

## Dimensional drawing



### Product

HalogenA IDE 500W E40 230V CL 1CT/6

IDE 500W E40 230V T38 CL

