



# **Halogen reflector**

### **ELD 150W 21V 24PK**

Philips' halogen reflector lamps offer the ideal no-fuss solution for a wide variety of medical, projection and scientific illumination systems. Their proven reliability makes them ideal for retrofit installations. The burners are precisely aligned for optimal light performance. Dichroic reflectors ensure heat dissipation towards the back of the optical system, which helps the optical system remain within temperature limits. A special blue-filter version blocking out unwanted light above 700 nm is available for dental curing applications. In addition, you get all the proven advantages of halogen technology such as a CRI of 100 – the same as natural sunlight for the best possible color rendering. Halogen lamps also create a comfortable warm white light, and they maintain their high lumen output with almost no lumen reduction throughout their lifetime.

#### **Product data**

General Information		
Cap-Base	GX5.3 [GX5.3]	
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]	
Life to 50% Failures (Nom)	40 hour(s)	
Light Technical		
Color rendering index (CRI)	100	
Operating and Electrical		
Power Consumption	150 W	
Voltage (Nom)	21 V	
Voltage (Nom)	21 V	
Controls and Dimming		
Dimmable	Yes	

Mechanical and Housing	
Bulb Material	Quartz-UV Open
Reflector Finish	Stippled
Bulb Shape	R50 [R 50mm]
Product Data	
Order product name	ELD 150W 21V 24PK
Full product name	ELD 150W 21V 24PK
Full product code	871150041060330
Order code	316182
Material Nr. (12NC)	923921319894
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500410603

8711500419040


Datasheet, 2023, August 30 data subject to change

Numerator - Packs per outer box

EAN/UPC - Case

# Halogen reflector

## Dimensional drawing



Product	D (max)	C (max)
ELD 150W 21V 24PK	2 inch	1-3/4 inch

