



Halogen non-reflector

EVD 7787 36V 400W G6,35 C1

Low-voltage quartz halogen capsule lamps


Product data

General Information	
Cap base	G6.35 [G6.35]
Philips code	7787
ANSI Code	EVD
LIF code	A1/239
Operating position	S90 [Standing +/-90D or Base Down (BDH)]
Main application	Projection
Life to 50% failures (nom.)	100 h
Light Technical	
Luminous flux (rated) (nom.)	14790 lm
Correlated colour temperature (nom.)	3400 K
Color rendering index (nom.)	100
Operating and Electrical	
Power (Rated) (Nom)	400 W
Voltage (Nom)	36 V
Mechanical and Housing	
Bulb material	Quartz-UV Open

Filament shape	Flat
Filament dimensions WxH	10.0x5.0
Luminaire Design Requirements	
Bulb temperature (max.)	900 °C
Pinch temperature (max.)	400 °C
Product Data	
Full product code	871150018712338
Order product name	7787 400W G6.35 36V 1CT/3X8F
EAN/UPC – product	8711500187123
Order code	18712338
Local Code	A1239
Numerator – quantity per pack	1
Numerator – packs per outer box	24
Material no. (12NC)	924031323306
Net weight (piece)	0.008 kg

Halogen non-reflector

Dimensional drawing



7787 400W G6.35 36V

Product	D (max)	L (min)	L (max)	L	P (max)	P	P (min)
7787 400W G6.35 36V 1CT/ 3X8F	18 mm	35.75 mm	36.25 mm	36 mm	1.05 mm	1 mm	0.95 mm

