



Halogen non-reflector

FCS-X 100 PACK

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.

Product data

General Information	
Base	G6.35 [G6.35]
Philips Code	7158XHP
ANSI Code	FCS
LIF Code	A1/216
Operating Position	Base Down +/- 90 D [Base Down +/- 90 D]
Main Application	Projection
Life to 50% Failures (Nom)	40 h

Light Technical	
Luminous Flux (Rated) (Nom)	6000 lm
Correlated Color Temperature (Nom)	3450 K
Color Rendering Index (Nom)	100

Operating and Electrical	
Power (Rated) (Nom)	150 W
Voltage (Nom)	24 V


Mechanical and Housing	
Bulb Material	Quartz-UV Open
Filament Shape	Flat
Filament Dimensions WxH	5.8 x 2.9

Luminaire Design Requirements	
Bulb Temperature (Max)	900 °C
Pinch Temperature (Max)	400 °C

Product Data	
Order product name	7158XHP 150W G6.35 24V 1CT/10X10F
EAN/UPC - Product	8711500410207
Order code	231746
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	100
Material Nr. (12NC)	924031720503
Net Weight (Piece)	0.004 kg

Halogen non-reflector

Dimensional drawing



Product

7158XHP 150W G6.35 24V 1CT/10X10F

7158XHP 150W G6.35 24V

