

# PHILIPS

# Lighting



## Capsuleline

### CAPS 100W GY6.35 12V CL 4000H 1CT/10X10F

Single-ended low-voltage halogen capsule giving crisp white halogen light


#### Product data

General Information	
Cap base	GY6.35 [ GY6.35]
Philips code	13100
Operating position	UNIVERSAL [ Any/Universal]
Nominal lifetime (nom.)	4000 h
Switching cycle	16000X
Light Technical	
Luminous flux (nom.)	1850 lm
Luminous flux (rated) (nom.)	1850 lm
Correlated colour temperature (nom.)	3000 K
Luminous efficacy (rated) (nom.)	22 lm/W
Color rendering index (nom.)	100
LLMF at end of nominal lifetime (min.)	80 %
Operating and Electrical	
Power (Rated) (Nom)	100.0 W
Lamp current (nom.)	8.33 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	instant full light
Power factor (nom.)	1
Voltage (Nom)	12 V
Controls and Dimming	
Dimmable	yes

Mechanical and Housing	
Bulb finish	Clear (CL)
Cap base information	15
Approval and Application	
Energy efficiency label (EEL)	D
Energy Consumption kWh/1000 h	106 kWh
Luminaire Design Requirements	
Bulb temperature (max.)	900 °C
Pinch temperature (max.)	350 °C
Product Data	
Full product code	871150040215850
Order product name	Capsuleline 100W GY6.35 12V CL 4000h 1CT/ 10X10F
EAN/UPC – product	8711500402158
Order code	40215850
Local Code	13100
Numerator – quantity per pack	1
Numerator – packs per outer box	100
Material no. (12NC)	924040017101
Net weight (piece)	2.300 g
ILCOS Code	HSG/C/UB-100-12-GY6.35

# Capsuleline

## Dimensional drawing



CAP SU 13100 100W GY6.35 12V CL

Product	D (max)	L	C (max)
Capsuleline 100W GY6.35 12V CL 4000h 1CT/ 10X10F	12 mm	30 mm	44 mm

