



Capsuleline

CAPS 100W GY6.35 12V CL 4000H 1CT/10X10F


Single-ended low-voltage halogen capsule giving crisp white halogen light

Product data

General Information	
Cap base	GY6.35 [GY6.35]
Operating position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	4,000 h
Switching Cycle	16,000
Rated Lifetime (Hours)	4,000 h
Lighting Technology	Halogen
Light Technical	
Luminous Flux	1,850 lm
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	22 lm/W
Colour rendering index (CRI)	100
Operating and Electrical	
Power Consumption	100.0 W
Lamp current (nom.)	8.33 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light	Instant full light s
Power Factor (Fraction)	1
Voltage (nom.)	12 V
Voltage (nom.)	12 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	T11 [T 11 mm]
Approval and Application	
Energy consumption kWh/1,000 hours	106 kWh
Product Data	
Order product name	Caps 100W GY6.35 12V CL 4000h 1CT/10X10F
Full product name	CAPS 100W GY6.35 12V CL 4000H 1CT/10X10F
Full EOC	871150040215850
Order code	40215850
Material no. (12 NC)	924040017101
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500402158
Numerator – packs per outer box	100
EAN/UPC - Case	8711500425713

Dimensional drawing



Product	D (max)	L	C (max)
Caps 100W GY6.35 12V CL 4000h 1CT/10X10F	12 mm	30 mm	44 mm

