



Capsuleline

CAPS 50W GY6.35 12V CL 4000H 1CT/10X10F

Single-ended low-voltage halogen capsule giving crisp white halogen light


Product data

General Information	
Cap base	GY6.35 [GY6.35]
Philips code	13102
Operating position	UNIVERSAL [Any/Universal]
Nominal lifetime (nom.)	4000 h
Switching cycle	16000X
Light Technical	
Luminous flux (nom.)	880 lm
Luminous flux (rated) (nom.)	880 lm
Correlated colour temperature (nom.)	3000 K
Luminous efficacy (rated) (nom.)	17.2 lm/W
Color rendering index (nom.)	100
LLMF at end of nominal lifetime (min.)	80 %
Operating and Electrical	
Power (Rated) (Nom)	50.0 W
Lamp current (nom.)	4.25 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	instant full light
Power factor (nom.)	1
Voltage (Nom)	12 V
Controls and Dimming	
Dimmable	yes

Mechanical and Housing	
Bulb finish	Clear (CL)
Cap base information	15
Approval and Application	
Energy efficiency label (EEL)	C
Energy Consumption kWh/1000 h	53 kWh
Luminaire Design Requirements	
Bulb temperature (max.)	900 °C
Pinch temperature (max.)	350 °C
Product Data	
Full product code	871150040217250
Order product name	Capsuleline 50W GY6.35 12V CL 4000h 1CT/10X10F
EAN/UPC – product	8711500402172
Order code	40217250
Local Code	13102
Numerator – quantity per pack	1
Numerator – packs per outer box	100
Material no. (12NC)	924040217101
Net weight (piece)	3.750 g
ILCOS Code	HSG/C/UB-50-12-GY6.35

Capsuleline

Dimensional drawing



Product	D (max)	L	C (max)
Capsuleline 50W GY6.35 12V CL 4000h 1CT/ 10X10F	12 mm	30 mm	44 mm

CAP SU 13102 50W GY6.35 12V CL

