



Capsuleline

CAPS 20W GY6.35 12V CL 4000H 1CT/10X10F

Single-ended low-voltage halogen capsule giving crisp white halogen light

Product data


General Information Cap base Operating position Nominal lifetime	GY6.35 [GY6.35] UNIVERSAL [Any or Universal (U)]		
Operating position			
	UNIVERSAL [Any or Universal (U)]		
Naminal lifetime	UNIVERSAL [Any or Universal (U)]		
Nominal medine	4,000 h		
Switching Cycle	16,000		
Rated Lifetime (Hours)	4,000 h		
Lighting Technology	Halogen		
Light Technical			
Luminous Flux	300 lm		
Correlated Colour Temperature	3000 K		
Luminous efficacy (rated) (nom.)	15 lm/W		
Colour rendering index (CRI)	100		
Operating and Electrical			
Power Consumption	20.0 W		
Lamp current (nom.)	1.66 A		
Starting time (nom.)	0.0 s		
Warm-up time to 60% light	Instant full light s		
Power Factor (Fraction)	1		
Voltage (nom.)	12 V		
Voltage (nom.)	12 V		

Controls and Dimming			
Dimmable	Yes		
Mechanical and Housing			
Lamp Finish	Clear		
Bulb shape	T11 [T 11 mm]		
Approval and Application			
Energy consumption kWh/1,000 hours	21 kWh		
Product Data			
Order product name	Caps 20W GY6.35 12V CL 4000h 1CT/10X10F		
Full product name	CAPS 20W GY6.35 12V CL 4000H 1CT/10X10F		
Full EOC	871150040219650		
Order code	40219650		
Material no. (12 NC)	924040417101		
Local order code	13104		
SAP numerator – quantity per pack	1		
EAN/UPC — Product/Case	8711500402196		
Numerator – packs per outer box	100		
EAN/UPC - Case	8711500425782		

Datasheet, 2023, April 30 data subject to change

Capsuleline

Dimensional drawing



Product	D (max)	L	C (max)
Caps 20W GY6.35 12V CL 4000h 1CT/10X10F	12 mm	30 mm	44 mm

