



# Halogen Low Voltage

## 6423XHP FO 150W GZ6.35 15V 1CT/10X5F

The long lifetime of most of the Halogen Low Voltage lamps is further extended by the unique P3 technology developed by Philips. This allows the lamp to be used at higher temperatures, thereby extending the lamp's lifetime, reducing early failures, and resulting in fewer maintenance man hour costs. P3 also ensures consistency of high-quality light output, and allows the lamp to be used in any burning position, which enables more compact fixture designs. In addition, the compact filament produces a clean white light and high beam intensity for true natural colors on stage and without any hotspots.

### Product data

General Information	
Cap base	GZ6.35 [ GZ6.35]
Philips code	6423XHP FO
ANSI Code	EFR
LIF code	A1/232
Operating position	P90/P15
Main application	Projection
Life to 50% failures (nom.)	50 h
J code	-

Light Technical	
Luminous flux (nom.)	950 lm
Correlated colour temperature (nom.)	3380 K
Color rendering index (nom.)	100

Operating and Electrical	
Power (Rated) (Nom)	150 W
Voltage (Nom)	15 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Cap base information	na [ -]
Bulb material	Quartz-UV Open
Reflector finish	-
Filament shape	-
Filament dimensions WxH	-

Luminaire Design Requirements	
Bulb temperature (max.)	900 °C
Pinch temperature (max.)	400 °C
Working distance WD	32 mm


Product Data	
Full product code	871150041182260
Order product name	6423XHP FO 150W GZ6.35 15V 1CT/10X5F
EAN/UPC – product	8711500411822

## Halogen Low Voltage

Order code	41182260
Numerator – quantity per pack	1
Numerator – packs per outer box	50
Material no. (12NC)	924044218504

Net weight (piece)	0.024 kg
--------------------	----------

### Dimensional drawing



6423XHP FO 150W GZ6.35 15V

### Product

6423XHP FO 150W GZ6.35 15V 1CT/10X5F

