



# Halogen reflector

## 6423FO 150W GZ6.35 15V 1CT

Quartz halogen lamps with integral reflector which serves as an efficient mirror condenser system

### Product data

General Information	
Cap base	GZ6.35
Operating position	P90/P15
Life to 50% failures (nom.)	50 h
Light Technical	
Luminous Flux	840 lm
Correlated Colour Temperature	3380 K
Colour rendering index (CRI)	100
Operating and Electrical	
Power Consumption	150 W
Voltage (nom.)	15 V
Voltage (nom.)	15 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb material	Quartz-UV Open
Reflector finish	-
Bulb shape	R50 [R 50 mm]
Product Data	
Order product name	6423FO 150W GZ6.35 15V 1CT/10X5F
Full product name	6423FO 150W GZ6.35 15V 1CT
Full EOC	871150040971360
Order code	40971360
Material no. (12 NC)	924048218504
Local order code	A1232
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500409713
Numerator – packs per outer box	50
EAN/UPC - Case	8711500419231

# Halogen reflector

## Dimensional drawing



Product	D (max)	C (max)
6423FO 150W GZ6.35 15V 1CT/10X5F	50 mm	42 mm

