



Appliance Sewing Machine Tubular

Appliance 20W B15d 230V T22X51 CL SM 1CT

Tubular incandescent vacuum lamp


Product data

General Information	
Cap-Base	B15
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Switching Cycle	4,000
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	120 lm
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	20.0 W
Lamp Current (Nom)	0.09 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230 V
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T22X51
Approval and Application	
Energy Consumption kWh/1000 h	20 kWh
Product Data	
Order product name	Appl 20W B15d 230V T22X51 - CL SM - 1CT
Full product name	Appliance 20W B15d 230V T22X51 CL SM 1CT
Full product code	871150025023050
Order code	25023050
Material Nr. (12NC)	924132044240
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500250230
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500251336

Appliance Sewing Machine Tubular

Dimensional drawing



Product	D (max)	C (max)
Appl 20W B15d 230V T22X51 - CL SM - 1CT	22 mm	52 mm

