



PAR56 and PAR64

PAR64 1000W 240V VNSP


These self-contained spotlights are ideal for intensifying the visual experience in all kinds of clubs, that is because their accurate beam control picks out even the smallest of details even over long distances. This beam control makes the PAR 56 and PAR 64 excellent for long-range light projections. In addition, the universal burning feature provides complete flexibility of luminaires angle and position, while the front glass of the PAR56 provides thermal and physical protection. The result? Complete creative freedom to achieve the desired effect. Immediate re-strike also ensures instant resumption of entertainment after any power interruption.

Product data

General Information		Mechanical and Housing	
Cap-Base	GX16D [GX16d]	Bulb Shape	PAR64 [PAR 8inch/200mm]
Operating Position	UNIVERSAL [Any or Universal (U)]	Product Data	
Nominal lifetime	300 h	Order product name	PAR64 1000W 240V VNSP
Light Technical		Full product name	PAR64 1000W 240V VNSP
Beam Angle (Nom)	11 degree(s)	Full product code	871150044060010
Correlated Color Temperature (Nom)	3200 K	Local code description	CP60
Operating and Electrical		Order code	924783245504
Power Consumption	1,000 W	Material Nr. (12NC)	924783245504
Voltage (Nom)	240 V	Local order code	CP60
Voltage (Nom)	240 V	Numerator - Quantity Per Pack	1
Controls and Dimming		EAN/UPC - Product/Case	8711500440600
Dimmable	Yes	Numerator - Packs per outer box	6
		EAN/UPC - Case	8711500440617

PAR56 and PAR64

Dimensional drawing



Product	D (max)	C (max)
PAR64 1000W 240V VNSP	204 mm	150 mm

