



MASTERLine ES

MASTERLine ES 20W GU5.3 12V 36D 1CT/4X5F

MASTER dichroic coated low-voltage halogen reflector lamp with EcoBoost technology. Most energy-efficient dichroic lamp on the market.

Product data

General Information	
Cap base	GU5.3 [GU5.3]
Philips code	18133
Operating position	UNIVERSAL [Any/Universal]
Nominal lifetime (nom.)	5000 h
Switching cycle	20000X

Light Technical	
Beam Angle (Nom)	36 °
Luminous flux (rated) (nom.)	300 lm
Luminous intensity (max.)	1000 cd
Rated beam angle	36 °
Correlated colour temperature (nom.)	3000 K
Color rendering index (nom.)	100
LLMF at end of nominal lifetime (min.)	80 %
Luminous Flux in 90° Cone (Rated)	300 lm

Operating and Electrical	
Power (Rated) (Nom)	20.0 W
Lamp current (nom.)	2 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	instant full light
Power factor (nom.)	1
Voltage (Nom)	12 V

Controls and Dimming	
Dimmable	yes


Approval and Application	
Energy efficiency label (EEL)	B
Energy Consumption kWh/1000 h	21 kWh

Luminaire Design Requirements	
Bulb temperature (max.)	250 °C
Cap base temperature (max.)	350 °C

Product Data	
Full product code	871150041367371
Order product name	MASTERLine ES 20W GU5.3 12V 36D 1CT/4X5F
EAN/UPC – product	8711500413673
Order code	41367371
Local Code	18133
Numerator – quantity per pack	1
Numerator – packs per outer box	20
Material no. (12NC)	924895017101
Net weight (piece)	30.000 g
ILCOS Code	HRGS-20-12-GU5.3-50/36

MASTERLine ES



Dimensional drawing



Product	D (max)	C1 (max)
MASTERLine ES 20W GU5.3 12V 36D 1CT/4X5F	51 mm	50.5 mm

MLES 18133 20W GU5.3 12V MR16 36D

Photometric data



Consumer Lamps, Halogen, Spectral power distribution

