



# MASTERLine ES

## MASTERLine ES 30W GU5.3 12V 36D 1CT/4X5F

MASTER dichroic coated low-voltage halogen reflector lamp with EcoBoost technology. Most energy-efficient dichroic lamp on the market.

### Product data


General Information	
Cap base	GU5.3 [ GU5.3]
Philips code	18136
Operating position	UNIVERSAL [ Any/Universal]
ANSI code halogen	na [ not applicable]
Nominal lifetime (nom.)	5000 h
Switching cycle	20000X
Light Technical	
Beam Angle (Nom)	36 °
Luminous flux (rated) (nom.)	540 lm
Luminous intensity (max.)	1600 cd
Rated beam angle	36 °
Correlated colour temperature (nom.)	3000 K
Color rendering index (nom.)	100
LLMF at end of nominal lifetime (min.)	80 %
Luminous Flux in 90° Cone (Rated)	540 lm
Operating and Electrical	
Power (Rated) (Nom)	30.0 W
Lamp current (nom.)	3 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	instant full light
Power factor (nom.)	1
Voltage (Nom)	12 V

Controls and Dimming	
Dimmable	yes
Approval and Application	
Energy efficiency label (EEL)	B
Energy Consumption kWh/1000 h	32 kWh
Luminaire Design Requirements	
Bulb temperature (max.)	380 °C
Cap base temperature (max.)	350 °C

Product Data	
Full product code	871150041378971
Order product name	MASTERLine ES 30W GU5.3 12V 36D 1CT/4X5F
EAN/UPC – product	8711500413789
Order code	41378971
Local Code	14582
Numerator – quantity per pack	1
Numerator – packs per outer box	20
Material no. (12NC)	924895317101
Net weight (piece)	30.000 g
ILCOS Code	HRGS-30-12-GU5.3-50/36

# MASTERLine ES



## Dimensional drawing



Product	D (max)	C1 (max)
MASTERLine ES 30W GU5.3 12V 36D 1CT/4X5F	51 mm	50.5 mm

MLES 18136 30W GU5.3 12V MR16 36D

## Photometric data



Consumer Lamps, Halogen, Spectral power distribution

