



# Halogen Low Voltage

## ELC/10H 6 250W 24V 24PK

The long lifetime of most of the Halogen Low Voltage lamps is further extended by the unique P3 technology developed by Philips. This allows the lamp to be used at higher temperatures, thereby extending the lamp's lifetime, reducing early failures, and resulting in fewer maintenance man hour costs. P3 also ensures consistency of high-quality light output, and allows the lamp to be used in any burning position, which enables more compact fixture designs. In addition, the compact filament produces a clean white light and high beam intensity for true natural colors on stage and without any hotspots.

### Product data


General Information	
Base	GX5.3 [ GX5.3]
Philips Code	13163
ANSI Code	ELC-10H
LIF Code	A1/259-10H
Operating Position	Universal [ Universal]
Main Application	Disco/Theatre
Life to 50% Failures (Nom)	1000 h
Light Technical	
Correlated Color Temperature (Nom)	3400 K
Color Rendering Index (Nom)	100
Operating and Electrical	
Power (Rated) (Nom)	250 W
Voltage (Nom)	24 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Material	Quartz-UV Open
Reflector Finish	Smooth
Filament Dimensions WxH	-
Luminaire Design Requirements	
Bulb Temperature (Max)	900 °C
Pinch Temperature (Max)	400 °C
Working Distance WD	31.7 mm
Product Data	
Order product name	ELC/10H 250W GX5.3 24V 1CT/24
EAN/UPC - Product	8711500436863
Order code	136580
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	24

## Halogen Low Voltage

Material Nr. (12NC)	924913220540
Net Weight (Piece)	0.024 kg

### Dimensional drawing



13163 ELC/10H 250W GX5.3 24V

Product	D (max)	C (max)
ELC/10H 250W GX5.3 24V 1CT/24	50 mm	44.5 mm

