



Lumiblade OLED Panel GL

OLED Panel Brite FL300L wm A0

High brightness functional lighting OLED panels.

Warnings and Safety

• OLEDs must be used in conjunction with suitable electronics that disconnect the OLED from the power supply in case of a short circuit. Use of Short Circuit Protection required.

Product data


Light Technical					
Luminous Flux	190 lumen				
Life to 70% Lumen Maintenance	10,000 hour(s)				
Correlated Color Temperature (Nom)	2500 K				
Luminous Efficacy (Rated) (Max)	30 lm/W				
Luminous Efficacy (Rated) (Min)	20 lm/W				
Color rendering index (CRI)	80				
Operating and Electrical					
Input Voltage	20.0 V				
Power Consumption	7.4 W				
Lamp Current (Nom)	368 mA				
Controls and Dimming					
Dimmable	Yes				

Approval and Application				
Approval Marks	CE marking RoHS compliance			
Product Data				
Full product code	871869653240900			
Order product name	OLED Panel Brite FL300L wm A0			
Order code	925400013001			
Numerator - Quantity Per Pack	1			
Numerator - Packs per outer box	10			
Material Nr. (12NC)	925400013001			
Full product name	OLED Panel Brite FL300L wm A0			
EAN/UPC - Case	8718696532416			
EAN/UPC - Product/Case	8718696532409			

Datasheet, 2023, September 4 data subject to change

Lumiblade OLED Panel GL

Dimensional drawing



Product	C1	A1	А3	B1	В3
OLED Panel Brite FL300L wm A0	1.1 mm	240.6 mm	222.0 mm	62.7 mm	46.0 mm



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.