



Halogen Classic Reflector

EcoClassic 42W E27 230V NR63 1CT/10 SRP

Philips Halogen Classic light bulbs offer the classical shapes you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.

Product data


General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Beam Angle (Nom)	30 degree(s)
Correlated Color Temperature (Nom)	2800 K
Color rendering index (CRI)	100
Luminous Flux in 90° Cone (Rated)	270 lm
Operating and Electrical	
Power Consumption	42.0 W
Lamp Current (Nom)	0.18 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230 V
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	NR63 [NR 63mm]
Approval and Application	
Energy Consumption kWh/1000 h	42 kWh
Product Data	
Order product name	EcoClassic 42W E27 230V NR63 1CT/10 SRP
Full product name	EcoClassic 42W E27 230V NR63 1CT/10 SRP
Full product code	872790025195104
Order code	25195104
Material Nr. (12NC)	925636044223
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900251951
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696462812

Datasheet, 2023, April 30 data subject to change

Halogen Classic Reflector

Dimensional drawing



Product	D (max)	C (max)
EcoClassic 42W E27 230V NR63 1CT/10 SRP	64 mm	104 mm



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.