



Halogen Classic Reflector

EcoClassic 28W E14 230V NR50 1CT/10 SRP

Philips Halogen Classic light bulbs offer the classical shapes you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.


Product data

General Information	
Cap-Base	E14 [E14]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Beam Angle (Nom)	30 degree(s)
Correlated Color Temperature (Nom)	2800 K
Color rendering index (CRI)	100
Luminous Flux in 90° Cone (Rated)	136 lm
Operating and Electrical	
Power Consumption	28.0 W
Lamp Current (Nom)	0.12 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230 V
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	NR50 [NR 50mm]
Approval and Application	
Energy Consumption kWh/1000 h	28 kWh
Product Data	
Order product name	EcoClassic 28W E14 230V NR50 1CT/10 SRP
Full product name	EcoClassic 28W E14 230V NR50 1CT/10 SRP
Full product code	872790025274304
Order code	25274304
Material Nr. (12NC)	925640044235
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900252743
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696462782

Halogen Classic Reflector

Dimensional drawing



Product	D (max)	C (max)
EcoClassic 28W E14 230V NR50 1CT/10 SRP	51 mm	86.5 mm

