



# Halogen Classic Reflector

## EcoClassic 28W E14 230V NR50 1CT/10 SRP

Philips Halogen Classic light bulbs offer the classical shapes you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.

### Product data

General Information	
Cap-Base	E14 [ E14]
Operating Position	UNIVERSAL [ Any or Universal (U)]
Nominal Lifetime (Nom)	2000 h
Switching Cycle	8000X

Light Technical	
Beam Angle (Nom)	30 °
Luminous Flux (Rated) (Nom)	136 lm
Luminous Intensity (Max)	300 cd
Rated Beam Angle	30 °
Colour Temperature, horizontal (Nom)	2800 K
Colour Rendering Index horiz (Nom)	100
LLMF at End of Nominal Lifetime (Min)	80 %
Luminous Flux in 90° Cone (Rated)	136 lm

Operating and Electrical	
Power (Rated) (Nom)	28.0 W
Lamp Current (Nom)	0.12 A
Starting Time (Nom)	0.0 s
Warm Up Time to 60% Light (Nom)	instant full light
Power Factor (Nom)	1

Voltage (Nom)	230 V
---------------	-------

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted

Approval and Application	
Energy Efficiency Label	D
Energy Consumption kWh/1000 h	28 kWh


Luminaire Design Requirements	
Cap-Base Temperature (Max)	130 °C

Product Data	
Full product code	872790025274304
Order product name	EcoClassic 28W E14 230V NR50 1CT/10 SRP
EAN/UPC - Product	8727900252743
Order code	25274304
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10

# Halogen Classic Reflector

Material Nr. (12NC)	925640044235
Net Weight (Piece)	20.800 g

## Dimensional drawing




HalClass 28W E14 230V NR50 30D FR

## Product

EcoClassic 28W E14 230V NR50 1CT/10 SRP

## Photometric data



Consumer Lamps, Halogen, Spectral power distribution

