



TUV PL-S

TUV PL-S 5W/2P 1CT/6X10BOX

TUV PL-S lamps are compact UVC (germicidal) lamps used in residential water and air disinfection units. The compact size of the lamp allows for a small system design and design flexibility. TUV PL-S lamps offer constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy. Thanks to the single-ended lamp base, lamp replacement is easy.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.

Product data


General Information		Voltage (Nom)	
Cap-Base	G23 [G23]	35 V	
Useful Life (Nom)	9,000 hour(s)	Mechanical and Housing	
Light Technical		Bulb Shape	2XT12
Color Code	TUV	Approval and Application	
Color Designation	- [Not Specified]	Mercury (Hg) Content (Nom)	3.0 mg
Depreciation at Useful Lifetime	20 %	UV	
Operating and Electrical		UV-C Radiation at 100 hr	1.2 W
Power Consumption	5.5 W	Product Data	
Lamp Current (Nom)	0.18 A	Order product name	TUV PL-S 5W/2P 1CT/6X10BOX
Voltage (Nom)	35 V	Full product name	TUV PL-S 5W/2P 1CT/6X10BOX

TUV PL-S

Full product code	871150064248680
Order code	64248680
Material Nr. (12NC)	927900504007
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500642486


Numerator - Packs per outer box	60
EAN/UPC - Case	8711500642509

Dimensional drawing



Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
TUV PL-S 5W/2P 1CT/6X10BOX	13 mm	28 mm	67 mm	83 mm	105 mm

Photometric data



Spectral Power Distribution Colour - TUV PL-S 5W/2P 1CT/6X10BOX

